

DELO® KATIOBOND® DF698

UV-curing encapsulant for Smart-Card technology, dam for Dam&Fill

Base

- modified epoxy resin
- one-component, solvent-free, UV-curing, thixotropic

Use

- encapsulation of chip modules in the Dam&Fill method as Dam compound. We recommend DELO KATIOBOND 4670 as Fill compound forming a homogeneous unit with DELO KATIOBOND DF698
- especially suitable for smart card technology, e. g., phone or health insurance cards
- the system enables extremely short cycle times and, therefore, an increase in productivity and a decrease in production costs
- is highly tension-equalizing and, therefore, has a favorable effect in case of bending stress
- low corrosion potential due to high ion purity
- positively tested according to UL 94 HB
- compliant with RoHS directive 2015/863/EU
- halogen-free according to IEC 61249-2-21

Processing

- the adhesive is supplied ready for use; in case of cool storage, it must be ensured that the container is conditioned to room temperature before use
- the containers are conditioned at room temperature (max. 25 °C); the conditioning time is approx. 5 h for containers up to 610 ml and 7 h for containers up to 950 ml; additional heat addition is not allowed
- store in a cool place (0 °C to +10 °C)
- do not tumble the DAM material
- a variation of the flow properties is possible by a dispensing valve heating
- dispensing valves and product-bearing elements must be carefully cleaned before use, residues of other products must be completely removed; DELOTHEN EP as well as acetone are recommended to remove DELO KATIOBOND residues
- for further information please refer to our brochure "Smart Card"

Curing

- curing with UVA light in a recommended wavelength range of 320 - 400 nm
- high initial strength after irradiation; therefore, complete protective function
- after irradiation curing until final strength within 24 h at room temperature
- increased temperatures accelerate the reaction, lower temperature decelerate it
- increased intensities shorten the required irradiation time, lower intensities prolong it

Curing parameters

- dependent on the layer thickness of the DAM material, lamp type and irradiation intensity

Technical data

| | |
|---|------------------------|
| Color cured in a layer thickness of approx. 0.1 mm | light gray transparent |
| Color cured in a layer thickness of approx. 0.5 mm | light gray translucent |
| Filler content [weight %] | 43 |
| Filler particle size [μm] d 98 | ≤ 32 |
| Density [g/cm^3] DELO Standard 13 at room temperature (approx. 23 °C) | 1.4 |
| Viscosity [mPas] at 23 °C, Brookfield spindle/rpm 7/5 | 180000 |
| Thixotropy index | 5 |
| Minimal irradiation time [s] DELO Standard 37, DSC UVA intensity: 55 - 60 mW/cm ² DELOLUXcontrol, at 30 °C | 15 |
| Recommended irradiation time [s] UVA-intensity: 55 - 60 mW/cm ² DELOLUXcontrol | 60 |
| Recommended irradiation time [s] LED 365 nm, intensity: 150 - 160 mW/cm ² DELOLUXcontrol; at approx. 70 °C | 30 |
| Curing time until final strength [h] at room temperature (approx. 23 °C) after irradiation | 24 |
| Compression shear strength glass/glass [MPa] DELO Standard 5 UVA intensity: 55 - 60 mW/cm ² , DELOLUXcontrol, irradiation time: 60 s curing time: 24 h at room temperature (approx. 23 °C) | 28 |
| Compression shear strength glass/Al [MPa] DELO Standard 5 UVA intensity: 55 - 60 mW/cm ² , DELOLUXcontrol, irradiation time: 60 s curing time: 24 h at room temperature (approx. 23 °C) | 12 |
| Compression shear strength glass/FR4 [MPa] DELO Standard 5 UVA intensity: 55 - 60 mW/cm ² , DELOLUXcontrol, irradiation time: 60 s curing time: 24 h at room temperature (approx. 23 °C) | 23 |
| Compression shear strength glass/PC [MPa] DELO Standard 5 UVA intensity: 55 - 60 mW/cm ² , DELOLUXcontrol, irradiation time: 60 s curing time: 24 h at room temperature (approx. 23 °C) | 12 |
| Tensile strength [MPa] according to DIN EN ISO 527 layer thickness: 2 mm | 22 |
| Elongation at tear [%] according to DIN EN ISO 527 layer thickness: 2 mm | 20 |
| Young's modulus [MPa] according to DIN EN ISO 527 layer thickness: 2 mm | 160 |
| Shore hardness D according to DIN EN ISO 868 | 61 |

| | |
|--|----------|
| Decomposition temperature [°C] DELO Standard 36 | 298 |
| <i>Glass transition temperature</i> [°C] rheometer | 35 |
| Coefficient of linear expansion [ppm/K] TMA, in a temperature range of +30 to +150 °C | 147 |
| Shrinkage [vol. %] DELO Standard 13 UVA intensity: 52 - 58 mW/cm ² DELOLUXcontrol, irradiation time: 60 s, curing time: 24 h at room temperature (approx. 23 °C) | 2.9 |
| Water absorption [weight %] according to DIN EN ISO 62, 24 h at room temperature (approx. 23 °C) | 0.4 |
| Thermal conductivity [W/(m·K)] flash method standardised by ASTM E 1461 at 25 °C; layer thickness: 0.5 mm | 0.38 |
| Specific heat capacity [J/gK] flash method standardised by ASTM E 1461 at 25 °C | 1.35 |
| <i>Ion content Na+</i> [ppm] extraction | <10 |
| <i>Ion content K+</i> [ppm] extraction | <10 |
| <i>Ion content Cl-</i> [ppm] extraction | <10 |
| <i>Ion content F-</i> [ppm] extraction | <100 |
| Specific volume resistance [Ωcm] VDE 0303, part 3 specimen: diameter 120 mm, thickness 2 mm | >1xE13 |
| Surface resistance [Ω] VDE 0303, part 3 specimen: diameter 120 mm, thickness 2 mm | >1xE12 |
| Dielectric constant RF-IV method, 1 MHz, at 25 °C +/- 3 °C | 3.6 |
| Dielectric constant RF-IV method, 10 MHz, at 25 °C +/- 3 °C | 3.6 |
| Dielectric constant RF-IV method, 100 MHz, at 25 °C +/- 3 °C | 3.4 |
| Dielectric constant RF-IV method, 1 GHz, at 25 °C +/- 3 °C | 3.3 |
| Storage life at 0 °C to +10 °C in unopened original container | 6 months |

Instructions and advice

General

The data and information provided are based on tests performed under laboratory conditions. Reliable information about the behavior of the product under practical conditions and its suitability for a specific purpose cannot be concluded from this. It is the customer's responsibility to test the suitability of a product for the intended purpose by considering all specific requirements and by applying standards the customer deems suitable (e. g. DIN 2304-1). Type, physical and chemical properties of the materials to be processed with the product, as well as all actual influences occurring during transport, storage, processing and use, may cause deviations in the behavior of the product compared to its behavior under laboratory conditions. All data provided are typical average values or uniquely determined parameters measured under laboratory conditions. The data and information provided are therefore no guarantee for specific product properties or the suitability of the product for a specific purpose.

Nothing contained herein shall be construed to indicate the non-existence of any relevant patents or to constitute a permission, encouragement or recommendation to practice any development covered by any patents, without permission of the owner of this patent.

All products provided by DELO are subject to DELO's General Terms of Business. Verbal ancillary agreements are deemed not to exist.

Instructions for use

The instructions for use of DELO KATIOBOND are available on: www.DELO.de. We will be pleased to send them to you on demand.

Occupational health and safety

see material safety data sheet

Specification

The properties in italics are part of the specification. Ranges with clear limits are defined for them and others, where applicable. In the course of the QA test, each batch is tested for these properties and the maintenance of the limits is ensured. The measuring methods used can deviate from those specified in the data sheet. Details can be found in the QA test report.